

## UV-3C-T Integrator SQUARE SD

(also available for LED measurement up to 20 W/cm<sup>2</sup>)

- + special square design 80 x 80 mm / 3 x 3 inches
- + UV-A intensity mW/cm<sup>2</sup> + UV-A dose mJ/cm<sup>2</sup>
- + UV-B intensity mW/cm<sup>2</sup> + UV-B dose mJ/cm<sup>2</sup>
- + UV-C intensity mW/cm<sup>2</sup> + UV-C dose mJ/cm<sup>2</sup>
- + \*UV-V intensity mW/cm<sup>2</sup> + UV-V dose mJ/cm<sup>2</sup>
- + Full UV intensity mW/cm<sup>2</sup> + Full UV dose mJ/cm<sup>2</sup>
- + Permanent or triggered recording\*
- + temperature measuring
- + SD Memory Card
- + graphical and numerical display on a PC
- + re-chargeable accu cell
- + further spectral ranges upon request
- + available up to 20W/cm<sup>2</sup>
- + available with high speed sampling rate 0.0007s (1400/s)



The UV-3C-T Integrator SQUARE SD is a self-contained, high quality UV measuring instrument. It is designed to measure, record and display peak UV intensity, UV dosage and temperature in the UV curing process.

It is equipped with three different UV sensors and one temperature sensor for the individual measuring of

UV-A 315 – 410 nm  
UV-B 280 – 315 nm  
UV-C 230 – 280 nm  
UV-V 395 – 445 nm\*  
UV - 230 – 410 nm  
Temp 32 to 230° F / 0 to 110° C

With these three different UV-bands plus the total UV band, most of the measuring requirements of UV curing applications can be covered.

Due to its three different UV sensors and the integrated microprocessor the UV-3C-T can measure, record and display the peak of the UV-energy (mW/cm<sup>2</sup>) for each UV-band individually plus the peak of total UV energy. Additionally, this UV-Integrator is calculating the UV-dosage (mJ/cm<sup>2</sup>) of the UV energy supplied during the time of exposure of one measuring cycle. The UV-dosage is calculated for each UV-band (UV-A, UV-B and UV-C or UV-V) individually and as total Integral of UV-dosage over all three UV-bands. This allows to determine not only the total energy, but also how that energy is delivered, i.e., what intensity and dose at what UV-band.

An extra sensor measures temperatures from 32 to 230° F / 0 to 110° C

\*This Microprocessor Integrator features a selectable „triggered mode“, i.e. the 30 sec recording cycle starts within a 120 second readiness phase not before the incident UV-intensity exceeds 2 mW/cm<sup>2</sup>.

The sensors are on the back of the unit which also serves as a heat shield. After completion of the measuring cycle all measuring results can be scrolled through on the built in 2 x 16 digit LCD display.

A special AUTO-OFF feature that turns off the unit automatically after one minute serves as energy saving and extension of the battery service life.

This microprocessor integrator is equipped with an SD Memory Card Slot. All measuring data are stored and can be downloaded to a computer. The special evaluation software allows to show, edit and store a history of the measuring results of the entire measuring cycle as graphic and numeric charts (mW/cm<sup>2</sup>) and (mJ cm<sup>2</sup>) and (°C/°F) (option)

**Item 51.3.4. UV-3C-T Integrator SQUARE SD UV-A + UV-B + UV-C**

**Item 51.3.4.1. UV-3C-T Integrator SQUARE SD UV-A + UV-B + UV-V**

## UV-3C-T Integrator SQUARE SD

### Technical Data:

|                             |  |
|-----------------------------|--|
| Spectral ranges:            | UV-A 315 – 410 nm<br>UV-B 280 – 315 nm<br>UV-C 230 – 280 nm<br>UV-V 395 – 445 nm*<br>UV 230 – 410 nm |
| Temperature range (option): | 32 to 230° F / 0 to 110° C   |
| Max. Power Input            | 0 to 5,000 mW/cm <sup>2</sup>  |
| Measuring range:            | 0 to 2,000 mW/cm <sup>2</sup>  |
| Sampling rate:              | 0.01 sec (100/sec max.)  |
| Recording cycle:            | 90 sec.  |
| Readiness phase:            | 120 sec.   |
| Display range:              | 0 to 36,000 mJ/cm <sup>2</sup>   |
| Display:                    | LCD, 2 x 16 digits   |
| Power source:               | 3.7 V LiPO Accu  |
| Power consumption:          | 20 µA  |
| Accu service life:          | 1,000 re-charging cycles   |
| Dimensions:                 | 80 mm x 80 mm x 22 mm (3 1/8" x 3 1/8" x 7/8")   |
| Weight:                     | approx. 10 ounce (300 g)   |
| Operating temperature:      | 32° to 113° F / 0 to 45° C   |
| Heat protection:            | Heat shield on back plate  |
| Base Accuracy:              | ± 5 %  |

While on the conveyer belt, the UV-3C-T Integrator SQUARE SD can withstand max. 230° F / 110° C for up to 10 seconds. The temperature of the housing should not exceed 113° F / 45° C. Because of uneven radiation distribution of the UV light source and different type of construction of the measuring devices by different manufacturers, different readings may appear under the same measurement conditions.

### Calibration:

In order to keep its full function and precision it is recommended to have re-calibration done once per year. Re-calibration will also be necessary after change of battery. PTB traceable calibration with certificate

**\*also available up to 20 W/cm<sup>2</sup>, display resolution in relation to maximum power input**  
**\*also available with high-speed sampling rate 0.0007 (1400/sec)**

Subject to change without prior notice © 2014-01

### Special Feature:

Stores data on SD-Memory Card for the download of data to a Computer

