

UV-4C Cube Integrator

- + 3D measuring
- + UV-A intensity mW/cm² + UV-A dose mJ/cm²
- + UV-B intensity mW/cm² + UV-B dose mJ/cm²
- + UV-C intensity mW/cm² + UV-C dose mJ/cm²
- + UV-V intensity mW/cm² + UV-V dose mJ/cm²
- + Full UV intensity mW/cm² + Full UV dose mJ/cm²
- + Permanent or triggered recording*
- + SD Memory Card (option)
- + graphical and numerical display on a PC (option)
- + re-chargeable accu cell



The *UV-4C Cube Integrator* is a self-contained, high quality UV measuring instrument. It is designed to measure and display peak UV intensity and UV dosage in the UV curing process.

It is equipped with four different UV sensors for the individual measuring of

UV-A + UV-B + UV-C + UV-V

With these four different UV-bands plus the total UV band, most of the measuring requirements of UV curing applications can be covered.

Due to its four different UV sensors and the integrated microprocessor the UV-4C can measure, record and display the peak of the UV-energy (mW/cm²) for each UV-band individually plus the peak of total UV energy.

Additionally, this UV-Integrator is calculating the UV-dosage (mJ/cm²) of the UV energy supplied during the time of exposure of one measuring cycle. The UV-dosage is calculated for each UV-band (UV-A, UV-B and UV-C or UV-V) individually and as total Integral of UV-dosage over all three UV-bands. This allows to determine not only the total energy, but also how that energy is delivered, i.e., what intensity and dose at what UV-band.

*This Microprocessor Integrator features a selectable "triggered mode", i.e. the 30 sec recording cycle starts within a 120 second readiness phase not before the incident UV-intensity exceeds 2 mW/cm².

The sensors are on one side of the unit in different directions, while the display is on the opposite side. After completion of the measuring cycle the measuring results can be scrolled through on the built in 2 x 16 digit LCD display.

A special AUTO-OFF feature that turns off the unit automatically after one minute serves as energy saving and extension of the battery service life.

The *UV-4C Cube Integrator* is optionally available equipped with an SD-Card Slot and an evaluation software for downloading the data to a computer to show, edit and store a history of the measuring results of the entire measuring cycle as graphic charts (mW/cm²) and (mJ cm²)

The UV-4C Cube Integrator is available as follows:

Item 52.7. UV-4C Cube Microprocessor Integrator UV-A, UV-B, UV-C, UV-V

Subject to change without prior notice © 2014-01

UV-DESIGN (Office) Triebstrasse 3 63636 Brachttal GERMANY Tel.: +49 (0)6053 619824

Fax: +49 (0)6053 619820

(Office & Workshop) UV-DESIGN Fabrikstrasse 12 63636 Brachttal GERMANY Tel.: +49 (0)6053 8095431 Fax: +49 (0)6053 8095433



UV-4C Cube Integrator

Technical Data:

Spectral ranges: UV-A 315 – 410 nm

UV-B 280 – 315 nm UV-C 230 – 280 nm UV-V 395 – 445 nm UV 230 – 410 nm

Max. Power Input 0 to 5,000 mW/cm²

Display: LCD, 2x16 digits

Display range: 0 to 36,000 mJ/cm²

Measuring range: 0 to 2,000 mW/cm²

Sampling rate: 0.005 sec (200/sec)

Measuring period: 90 sec.

Readiness phase: 120 sec.

Power source: 3.7 V NiMH Accu-Pack, 70 mA, re-chargeable

Power consumption: 20 µA

Battery service life: 1,000 charging cycles

Dimensions: 2.4" x 2.4" x 2.4" (60 x 60 x 60 mm)

Weight: approx. 17.5 ounce (500 g)

Operating temperature: 0 to 113° F / 0 to 45° C

Heat protection: Heat shield

Base Accuracy: $\pm 5 \%$

While on the conveyer belt, the *UV-4C Cube Integrator* can withstand max. 230° F / 110° C for up to 10 seconds. The temperature of the housing should not exceed 113° F / 45° C.

Because of uneven radiation distribution of the UV light source and different type of construction of the measuring devices by different manufacturers, different readings may appear under the same measurement conditions.

Calibration:

In order to keep its full function and precision it is recommended to have re-calibration done once per year. Re-calibration will also be necessary after change of battery. PTB traceable calibration with certificate


*also available up to 20W/cm², display resolution in relation to maximum wattage


*also available with high speed sampling rate 0.0007s(1400/s)

Subject to change without prior notice © 2014-01

Option:
Stores data on
SD-Memory Card
for the download
of data

to a Computer





UV-DESIGN (Office) Triebstrasse 3 63636 Brachttal GERMANY Tel.: +49 (0)6053 619824 Fax: +49 (0)6053 619820 (Office & Workshop) UV-DESIGN Fabrikstrasse 12 63636 Brachttal GERMANY Tel.: +49 (0)6053 8095431 Fax: +49 (0)6053 8095433